

TABLET FRIABILITY TEST APPARATUS (LI-TFT-155)

APPLICATION :

The strength of a tablet plays a very important role in its marketing and dissolution. The mechanical strength of a tablet or granules can be determined by its hardness and through friability test.



FEATURES :

- Transparent acrylic drum for clear view.
- This drum has a acrylic blade.
- A fix 25 RPM Motor drives the unique Universal acrylic drum.
- Digital microprocessor based counter is provided to pre-set the revolution & to automatically stop the motor with alarm (optional feature).
- In Power failure, the memory of the microprocessor remember the time left and complete the cycle after power resumes (optional feature).
- Easy loading and unloading of the drum with positive grip is provided.

TECHNICAL SPECIFICATIONS :

| | | |
|---------------------------|--|-------------|
| Model : LI-TFT-155 | | |
| Types | Single Drum | Double Drum |
| Timer | Digital Timer | |
| Speed | With 25 RPM motor with digital display | |
| Drum Size | Universal Acrylic drum of 300mm diameter as per USP Standard | |
| Power | 230V AC, 50Hz | |

Models, Features and Specifications subject to change without notice.